

# **Sponges**

CS

Plato offers soldering accessories like sponges, tip tinner, and bottles to improve your soldering process and increase your tip life.

Request More Info





# Cellulose solder station sponges for Weller, Hakko, Pace and more

Plato® sponges are manufactured with pure cellulose (a wood derivative) which has the ability to absorb many times its weight in water. Also resistant to abrasion and tearing forces that occur during the tip wiping process. Cellular structure is designed to expand when wet, and retain water for long periods of time. Meets ANSI (J-STD-001B) for low sulphur content and fine porosity.

- · Extend tip life
- · Remove surface oxides
- · Remove excess solder

# **Product Dimensions**

# CS-1 Sponge - fits Weller

1.5" x 2.12" x 1" thick (38mm x 54mm x 25mm)

#### CS-9/625 Sponge - fits Hexacon

3.5" x 4.5" x 0.625" thick (89mm x 114mm x 16mm) 10 units/case

# **CS-14**

2.2" x 2.75" x 1" thick (55mm x 70mm x 25mm) 10 units/case

#### CS-14M Sponge w/multiple holes - fits Weller

2.2" x 2.75" x 1" thick (55mm x 70mm x 25mm) 10 units/case

#### CS-17 Sponge - cut-to-fit sheet

8.5" x 17" x 1" thick (216mm x 432mm x 25mm)

# CS-17/625 Sponge - cut-to-fit sheet

8.5" x 17" x 0.625" thick (216mm x 432mm x 16mm)



#### CS-36 Sponge - fits Hexacon

2.25" x 3.5" x 1" thick (57mm x 89mm x 25mm) 10 units/case

### CS-44 Sponge - fits Hakko

2.7" x 2.7" x 1" thick (69mm x 69mm x 25mm)

#### CS-44/625 Sponge - fits Hakko

2.7" x 2.7" x 0.625" thick (69mm x 69mm x 16mm)

# CS-47 Sponge - fits Metcal

2.1" x 3.2" x 1" thick (53mm x 81mm x 25mm) 10 units/case

#### CS-888H

2 3/8" dia x 2"L x 5/8" thick (60mm x 51mm x 17mm) 10 units/case

#### CS-888S

2 3/8" dia x 2"L x 5/8" thick (60mm x 51mm x 17mm)

# **Environmental Policy**

Techspray is committed to developing products to ensure a safer and cleaner environment. We will continue to meet and sustain the regulations of all federal, state and local government agencies.

# Resources

Techspray products are supported by a global sales, technical and customer services resources.

For additional technical information on this product or other Techspray products in the United States, call the technical sales department at 800-858-4043, email tsales@techspray.com or visit our web site at: <a href="www.techspray.com">www.techspray.com</a>.

### North America

Techspray P.O. Box 949 Amarillo, TX 79105 800-858-4043

Email: tsales@techspray.com

#### <u>Europe</u>

ITW Contamination Control Saffierlaan 5 2132 VZ Hoofddorp The Netherlands +31 88 1307 400 Email: info@itw-cc.com

#### Countries Outside US

Call to locate a distributor in your country.

Important Notice to Purchaser/User: The information in this publication is based on tests that we believe are reliable. The results may vary due to differences in tests type and conditions. We recommend that each user evaluate the product to determine its suitability for the intended application. Conditions of use are outside our control and vary widely. Techspray's only obligation and your only solution is replacement of product that is shown to be defective when you receive it. In no case will Techspray be liable for any special, incidental, or consequential damages based on breach of warranty, negligence or any other theory.

© 2016 Techspray, A Division of ITW