



# TG-LH-EE-90-5 Electronics Epoxy

Version 2.120320

## Electronics Epoxy

TG-LH-EE-90-5 is a one-part, off-white adhesive based on epoxy resins, designed especially for bonding electronic components. It cures quickly at elevated temperatures and has excellent adhesion to most PC boards and electronic components. It may be cured at 100°C or faster at 175°C and has no sagging. It has a stable pot life and long shelf life even at a room temperature of 25°C. Due to relatively low viscosity, it dispenses faster from syringes than other products on the market. It is highly thixotropic which can assist in controlling the flow of the adhesive.

## Features

Fast curing especially at higher temperatures  
Designed specifically for bonding electronic components  
Stable pot life with a long shelf life

## Applications

Epoxy adhesive for bonding ceramic, metals, and most plastics in electronics.

## Properties

- ✓ REACH Compliant
- ✓ ROHS Compliant

Property	TG-LH-EE-90-5	Unit	Test Method
Chemical type	Epoxy	-	-
Appearance	White paste	-	Visual
Mix ratio, by weight	One component	-	-
Shelf life, -20°C	12	Months	ASTM F2914
Pot life, 25°C	1	Week	ASTM F2914
Viscosity, CAP 2000+ viscometer, 25°C Cap-06@40rpm	24,000	cps	ASTM D1084
Thixotropic Index	1.8	-	-
Hardness cured 100°C for 2 hr	90	Shore D	ASTM D2240
Shear Strength	545	kgcm <sup>-2</sup>	ASTM D412
Water boil, wt gain, 100°C/1hr	0.35	%	-
Tg, DSC, cured 100°C for 2 hr	122	°C	-
Specific gravity	1.3	g/cm <sup>3</sup>	ASTM D792
CTE, alpha-1	59	ppm/°C	-
CTE, alpha-2	151	ppm/°C	-
Ionic Content, Cl	<50	ppm	-
Ionic Content, K	<50	ppm	-
Ionic Content, Na	<20	ppm	-
Dielectric Contant, 30MHz-1GHz	3.1-3.3	-	GB/1693-20017

## Standard Packaging

Size	Packaging	Volume (ml)
	EFD Syringe	5 ml
EFD Syringe	10 ml	
EFD Syringe	30 ml	

T-Global Technology Limited  
1 & 2 Cosford Business Park, Central Park,  
Lutterworth, Leicestershire LE17 4QU U.K.

Tel: +44 (0)1455 553 510  
Email: sales@tglobaltechnology.com  
Web: www.tglobaltechnology.com  
VAT #: GB 116 662 714



# TG-LH-EE-90-5 Electronics Epoxy

## Storage

Store in fridge at 2°C. Tightly close original container of unused product. Storing at lower temperatures down to -20°C may prolong shelf life beyond 6 months. However, it may take longer time to thaw the product.

## Recommended Cure

Temperature	Gel Time	Cure Time
100 °C	12 mins	2 hours
150 °C	2 mins	30 mins

## Guidelines for Use

1. Thaw the epoxy to room temperature (25°C) before use.
2. Dispense the epoxy by using a syringe.
3. Wipe off any excess uncured adhesive with a piece of dry cloth or tissue. Further cleaning may be achieved with tissue dabbed with iso-propanol-alcohol (IPA).
4. Cure the epoxy by heating at 100°C for 120 minutes in a convection oven. Curing at lower temperature will require a longer time.

\* Data for design engineer guidance only. Observed performance varies in application. Engineers are reminded to test the material in application.

**NOTICE:** The information contained herein is to the best of our knowledge true and accurate. However, since the varied conditions of potential use are beyond our control, all recommendations or suggestions are presented without guarantee or responsibility on our part and users should make their own test to determine the suitability of our products in any specific situation. This product is sold without warranty either expressed or implied, of fitness for a particular purpose or otherwise, except that this product shall be of standard quality, and except to the extent otherwise stated T-Global Technology Europe and North America's invoice, quotation, or order acknowledgment. We disclaim any and liability incurred in connection with the use of information contained herein, or otherwise. All risks of such are assumed by the user. Furthermore, nothing contained herein shall be construed as a recommendation to use any process or to manufacture or to use any product in conflict with existing future patents covering any product or material or its use.